

❖ **BM-500 GE / BB-500 GE** Progressive Scan



- *Member of C3 Basic series*
- *2456 (h) x 2058 (v) 3.45 μ m square pixels*
- *2/3" progressive scan – Monochrome and Bayer mosaic color versions*
- *15 frames/second with full resolution in continuous operation*
- *15 frames/second with external trigger and full resolution*
- *Increased frame rate with vertical binning (BM-500 GE) and partial scan*
- *Sequencer trigger mode for on-the-fly change of gain, exposure and ROI*
- *Edge Pre-Select and Pulse Width trigger modes*
- *Exposure time from 64 μ s to 2 sec. using Pulse Width Control trigger mode*
- *Programmable exposure from 64 μ s to 66 ms in Full Frame scan*
- *Several pre-processing functions for offloading host PC*
- *LVAL-synchronous/-asynchronous operation (auto-detect)*
- *Auto iris lens video output allows a wider range of light*
- *GigE Vision interface with 12, 10 or 8-bit output*
- *Programmable GPIO with opto-isolated inputs and outputs*
- *Comprehensive software tools and SDK for Windows XP/Vista*

GigE™
VISION




Specifications for BM-500 GE / BB-500 GE

Specifications	BM-500 GE / BB-500 GE
Sensor	2/3" progressive scan CCD
Pixel Clock	60 MHz
Frame rate full frame	15 frames/second
Active area	8.45 (h) x 7.07 (v)
Cell size	3.45 (h) x 3.45 (v)
Active pixels	2456 (h) x 2058 (v)
Color (BB-500 GE)	Raw Bayer output, host based interpolation
Read-out modes	Full 2456 (h) x 2058 (v) 15 fps 1/2 partial scan 2456 (h) x 1028 (v) 24 fps 1/4 partial scan 2456 (h) x 514 (v) 34 fps 1/8 partial scan 2456 (h) x 258 (v) 43 fps 2/3 partial scan 2456 (h) x 1372 (v) 20 fps Vertical binning 2456 (h) x 1039 (v) 22 fps* Region-of-interest (ROI) User definable. Memory read-out *Note: BM-500 GE only
Sensitivity (BM-500 GE)	0.34 Lux (On sensor, max. gain, shutter off, 50% video)
Sensitivity (BB-500 GE)	1.0 Lux (On sensor, max. gain, shutter off, 50% video)
S/N ratio	>50 dB (0 dB gain)
Video output	GigE Vision, 8-bit, 10-bit or 12-bit
Auto-iris lens video output	0.7 Vp-p, enabled by internal switch
Gain	Manual/Automatic Range -3 to 12 dB
Synchronization	Internal X-tal, External hardware trigger via GPIO Software trigger via GigE Vision
GPIO Module	Input/output switch Clock generator (one)
Pulse generators (four)	20-bit counter programmable for length, start point, stop point, repeat
Trigger modes	Pre-Select, Pulse Width, Frame Delay and Sequence
Electronic shutter	Pre-set shutter
Programmable exposure (PE)	1/15 and 1/30 to 1/10,000 in 10 steps
Exposure Time (Abs)	2L(64μs) to 2072 L (66.44ms) in 1L steps
Pulse Width	μsec – user definable. Same range as PE
Pre-processing functions	64μs to 2 sec. Output transfer functions (Gamma, multiple-point knee), Bayer white balance, L/R channel balancing, Blemish compensation
Control interface	Register based. GigE Vision / GenICam compliant
Functions controlled via GigE Vision interface	Shutter, Gain, Black Level, Trigger mode, Read-out mode, GPIO setup, ROI (GenICam mandatory functions)
GigE Vision streaming control	Packet size (1428 to 4040 bytes) Delayed (Frame) read-out, inter-packet delay
Indicators on rear panel	Power/Hardware trigger, GigE Link, GigE activity
Operating Temperature	-5°C to +45°C
Humidity (operation)	20 - 90% non-condensing
Storage temp./humidity	-25°C to +60°C / 20 to 90%
Vibration	10G (20Hz to 200 Hz XYZ)
Shock	70G
Regulations	CE (EN 61000-6-2, EN-61000-6-3), FCC part 15 class B, RoHS/WEEE
Power	12V DC +/-10%. 5.5W
Lens mount	C-mount
Dimensions (H x W x L)	55 x 55 x 55
Weight	200 g

Connector pin-out

DC In / GPIO




HIROSE HR10A-10R-12PB-01

Connector Pin-out

- | | |
|-------|---------------------------------|
| Pin 1 | GND |
| 2 | +12 V DC input |
| 3 | Opt IN 2 (-) / GND * |
| 4 | Opt IN 2 (+) / Iris Video out * |
| 5 | Opt IN 1 (-) |
| 6 | Opt IN 1 (+) |
| 7 | Opt Out 1 (-) |
| 8 | Opt Out 1 (+) |
| 9 | Opt Out 2 (-) |
| 10 | Opt Out 2 (+) |
| 11 | +12 V DC input |
| 12 | GND |


* Pins 3 and 4 can be configured by internal switch selection

GigE Vision interface Accepts RJ-45 with thumbscrews



- | | | | |
|-------|---------|---|---------|
| Pin 1 | TRD+(o) | 5 | TRD-(2) |
| 2 | TRD-(o) | 6 | TRD-(1) |
| 3 | TRD+(i) | 7 | TRD+(3) |
| 4 | TRD+(2) | 8 | TRD-(3) |

Spectral Response BM-500 GE




Ordering Information


BM-500 GE 2/3" Monochrome Progressive Scan Camera
BB-500 GE 2/3" Bayer Mosaic Color Progressive Scan Camera

Dimensions


Front view




Side view




Bottom view



Rear view



Spectral Response BB-500 GE



C3 Camera Suite » Unlimited Digital Switchability

Europe, Middle East & Africa
Phone +45 4457 8888
Fax +45 4491 8880

Asia Pacific
Phone +81 45 440 0154
Fax +81 45 440 0166

Americas
Phone (Toll-Free) 1 800 445 5444
Phone +1 408 383 0300

Visit our web site on www.jai.com



See the possibilities