




3rd Party Agilent 1200 Series Instrument Control

Dionex Chromeleon

Agilent 1200 Series Module	Product Number	Required Agilent Firmware Revision for:		
		6.60, Service Pack 9	6.70, Service Pack 6	6.80, Service Pack 3, driver update 2c
1200 Series Vacuum Degassers				
Micro Vacuum Degasser	G1379B	compatible	compatible	compatible
Vacuum Degasser	G1322A	compatible	compatible	compatible
1200 Series Pumps				
Isocratic Pump	G1310A	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Quaternary Pump	G1311A	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Binary Pump	G1312A	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Binary Pump SL	G1312B	B.01xx, A.06xx	B.01xx, A.06xx	A.06.04
1200 Series Injection Systems				
Standard Autosampler	G1329A	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Standard Autosampler SL	G1329B	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
High Performance Autosampler	G1367B	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
High Performance Autosampler SL	G1367C	B.01xx, A.06xx	B.01xx, A.06xx	A.06.03
High Performance Autosampler SL+	G1367D	not yet supported	not yet supported	not yet supported
Micro Well Plate Autosampler	G1377A	not yet supported	not yet supported	not yet supported
Thermostat for Autosampler	G1330B	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
1200 Series Thermostatted Column Compartments				
Thermostatted Column Compartment	G1316A	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Thermostatted Column Compartment SL	G1316B	B.01xx, A.06xx	B.01xx, A.06xx	A.06.04
Thermostatted Column Compartment SL+	G1316C	not yet supported	not yet supported	not yet supported
1200 Series Detectors				
Variable Wavelength Detector	G1314B	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Variable Wavelength Detector SL	G1314C	B.01xx, A.06xx	B.01xx, A.06xx	A.06.04
Variable Wavelength Detector	G1314D	not yet supported	not yet supported	not yet supported
Variable Wavelength Detector SL+	G1314E	not yet supported	not yet supported	not yet supported
Multiple Wavelength Detector	G1365B	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Multiple Wavelength Detector	G1365D	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Multiple Wavelength Detector SL	G1365C	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Diode Array Detector	G1315B	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Diode Array Detector	G1315D	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Diode Array Detector SL	G1315C	B.01xx, A.06xx	B.01xx, A.06xx	B.01.06
Fluorescence Detector	G1321A	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Refractive Index Detector	G1362A	B.01xx, A.06xx	B.01xx, A.06xx	B.01xx, A.06xx
Evaporative Light Scattering Detector	G4218A	not yet supported	not yet supported	not yet supported
1200 Series Fraction Collectors				
Fraction Collector	G1364C	not yet supported	not yet supported	not yet supported
1200 Series Valve Solutions				
2-position/6-port valve	G1158A	not yet supported	not yet supported	not yet supported
2-position/10-port valve	G1157A	not yet supported	not yet supported	not yet supported
12-position/13-port valve	G1160A	not yet supported	not yet supported	not yet supported
6-position column selection valve	G1159A	not yet supported	not yet supported	not yet supported

© Agilent Technologies Inc., 2009
Published March 1, 2009



Agilent Technologies